

PICKING BINS

25-304-20xx

Products Specifications

Material:	Conductive polypropylene copolymer
Colour:	Black
Density (at 23°C):	1.04 g/cm ³
Working Temperature	
Continuous:	approx 80-100°C
Short term:	approx 100-120°C
Surface resistance:	< 10 ⁴ Ω



Part-Number and Dimensions

Part Number	External Dimensions (mm)	Internal Dimensions (mm)	Capacity (L)	Weight (gr)
25-304-2001	85 x 95 x 45	63 x 91 x 44	0.25	48
25-304-2002	160 x 95 x 75	133 x 87 x 66	1	114
25-304-2003	230 x 140 x 130	193 x 126 x 110	3.8	248
25-304-2006	350 x 200 x 145	273 x 183 x 130	9.4	678
25-304-2005	350 x 200 x 200	270 x 179 x 185	12.5	848
25-304-2007	500 x 300 x 145	428 x 281 x 129	20	1374
25-304-2004	500 x 300 x 200	426 x 282 x 185	28	1534
25-304-2008	500 x 300 x 300	423 x 280 x 285	42	2374