

Project..... Comments.....

Fixture Type..... Prepared By.....

Product Description:

True short form GU10 and MR16 LED lamps. Smooth and linear dimming on most dimmers (dimmable versions). MR16 versions for use with electronic transformers and 12V DC LED drivers. High colour rendering index (Ra) >83. Life to 70% lumen maintenance - 30,000 hours. 2 Year guarantee.

Product Image & Dimensions:



Overall Diameter	50 mm
Overall Length	55 mm
Overall Height	55 mm

Product Specifications:

- Lamp Type: GU10
- Lamp Base: GU10
- Input Voltage (Min): 240 V
- Input Voltage (Max): 240 V
- Dimmable: No
- Beam Angle: 40 °
- Lifespan: 30000 hrs
- Overall Diameter: 50 mm
- Overall Length: 55 mm
- Overall Height: 55 mm
- Guarantee: 2 Years

Compliance & Approvals:



SKU Table and Ordering:

SKU Code	Wattage	Colour Temperature	Lumens	Candelas	Colour	EAN	Qty
AU-GU1060W/30	6 W	3000 K	280 lm	480 cd	White	5055155481766	
AU-GU1060W/40	6 W	4000 K	300 lm	515 cd	White	5055155482169	

Warranty:

For available warranty information for this product, please visit:

<http://gb.auroralighting.com/Products/Lamps/Economy-LED-Lamps/240V-GU10/240-GU10-6W-White-Non-dimmable-LED-Lamp.aspx>

UK Sales

16 Alban Park
Hatfield Road, St. Albans
United Kingdom
PH: +44 (0) 1727 83 66 11
FX: +44 (0) 1727 83 66 22

UK Distribution

Apex Park, 6 Little Burrows
Burrowfields, Welwyn Garden City
AL7 4SW
United Kingdom
PH: +44 (0) 1707 35 18 20
FX: +44 (0) 1727 35 18 21