

Features

- **Durable Construction:** Forged steel body for strength and longevity.
- **Precision Striking:** Turned copper tips for controlled impact and reduced rebound.
- **Protective Collar:** Nylon collar minimizes damage and wear during use.
- **Comfortable Grip:** Varnished ash wood handle for ergonomic handling and reduced fatigue.
- **Versatile Application:** Ideal for engineering, maintenance, and assembly tasks requiring non-sparking and non-marring strikes.

RS PRO Copper Mallet with Turned Copper Tips, Forged Steel Body, Nylon Collar & Varnished Ash Handle, 40mm Head Diameter

RS Stock No.: 0747549



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

The RS PRO Copper Mallet is designed for precision and durability in demanding industrial environments. Featuring turned copper tips for accurate striking, a forged steel body for strength, and a nylon collar for added protection, this mallet ensures reliable performance. The varnished ash wood handle provides a comfortable grip, making it suitable for extended use. Perfect for applications where controlled force and non-sparking properties are essential, such as in mechanical assembly, maintenance, and repair work.

General Specifications

Product Type	Copper Mallet
Head Material	Copper (Turned Tips)
Body Material	Forged Steel
Collar Material	Nylon
Handle Material	Varnished Ash Wood
Head Diameter	40 mm
Overall Length	320 mm
Head Length	105 mm