




## Panel Mounted Receptacles

### ■ DB Body Style



Series	A	B min/max.	C	C1	D	M	⌘	Torque [Nm]
102	18	0/3	11.0	1.0	11	9x0.5	11	1.3
103	21	0/4	11.5	1.5	14	12x1	14	2.5
1031	Please contact us for additional information							
104	26	0/3	14.5	2.5	19	16x1	19	4.5
105	33	0/7	19.0	2.0	22	18x1	22	6.0
106	Please contact us for additional information							
107	Please contact us for additional information							

### ■ DBEU / DBEE Body Styles



Series	A	B min/max.	C	C1	D	M	⌘ 1	Torque 1 [Nm]	⌘ 2
102	20	0/3.5	10.2	2.5	14	9x0.5	11	1.3	11
103	23	0/4.0	13.0	3.0	18	14x1	17	3.0	14
1031	24	0/4.0	12.0	3.0	19	14x1	17	3.0	15
104	30	0/3.5	16.0	4.0	22	16x1	19	4.5	17
105	32	0/5.0	19.0	4.0	27	18x1	22	6.0	22
106	50	0/6.5	25.5	7.0	40	32x1	TX00.106	15	-
107	47	0/5.0	24.0	5.0	45	35x1	TX00.107	16	38