

Datasheet

ENGLISH

RS PRO Panel Mounting printer

Stock No: 178-5734



This RS Pro panel mount printer features a Seiko brand fixed head thermal line printer mechanism with a guillotine auto-cutter and anti-blockage design. It also has a large paper capacity. It has an electrical rating of 9-24VDC +/- 10%/2A. Interfaces featured are RS232/Parallel + USB/RS485. This printer has a resolution of 8dpmm with 384 dots per line. Effective printing width 48mm. Print speed 100mm/s.

Features and Benefits

- Partial/full auto-cut
- 60mm big paper roll support
- Simple drop-in easy paper loading for operational efficiencies
- Data input RS232/Parallel + USB/RS485
- Compact dimensions; Height 109mm, of 101mm, depth 68mm
- Paper width is 57.5mm (+/- 0.5mm)
- Reliable long-life expectancy of MCBF 5 million lines.
- High speed printing 100mm/s.
- Robust, stylish design that is easily embedded into many devices.

Applications

- Receipt printing
- Medical/Healthcare equipment
- OEM Machines
- Test and measurement