

**BOSCH**

Invented for life

Product data sheet

Power tools for trade & industry

Combi Laser

PRO GCL 2-50



Compact and versatile for all levelling applications up to 50 metres

The most important data

Working range with receiver	50 m
Working range, value	15 m
Accuracy	± 0.3 mm/m

Part Number 0 601 066 F01

Technical data

Technical data

Laser diode	630 – 650 nm, < 1mW
Operating temperature	-10 – 50 °C
Storage temperature	-20 – 70 °C
Laser class	2
Working range, value	15 m
Working range with receiver	50 m
Accuracy	± 0.3 mm/m
Working range of laser points, max.	10 m (top), 10 m (bottom)
Self-levelling range	± 4°
Levelling time	4 s
Dust and splash protection	IP 54
Power supply	3 x 1.5 V LR6 (AA)
Operating time (max.)	6 h in cross line and point mode, 8 h in cross line mode, 12 h in line and point mode, 16 h in line mode, 22 h in point mode
Tripod thread	1/4", 5/8"
Weight, approx.	0.49 kg
Colour of laser line	red
Color of plumb points	red

Projection	2 lines / 2 points
Plumb point accuracy	± 0.7 mm/m
Compatible laser receivers	LR 6 + 7



Product data sheet

Power tools for trade & industry

Advantages:

- Horizontal and vertical laser lines and two centred plumb points with optimal visibility
- Receiver mode that allows you to work with the Bosch laser receiver LR 6 and LR 7 for a working range up to 50 metres
- Flexible to use with rotating RM 1 Professional multifunctional mount for aligning the laser lines and for versatile mounting of the tool



You can find more information about the deviations in the following link: <https://www.bosch-professional.com/gb/en/wac/>

