



ENGLISH

Datasheet

## RS Pro PET D-sub Connector Backshell, 37 Way, Strain Relief

RS Stock No: **544-4411**



### Product Details

RS Pro screwdown cover with jackscrews has 37 number of contact with C D-sub shell size in a PET housing. This straight screwdown cover is suitable for use with most standard and crimp D-connectors. This provides locking action with jack screws in combination with female screwlock assembly. The cover allows you for side or top cable entry through removable knockouts and cable retention. It is supplied with 2 jack screws, self tapping cover screws and cable clamp.

### Features and Benefits

- Covers with removable knockouts allow for either top or side cable entry
- 2 jack screws, self-tapping cover screws and cable clamp
- Offers locking action with jack screws in combination with female screwlock assembly
- Side or top cable entry via removable knockouts and cable retention



ENGLISH

### Specifications:

Body Orientation	Straight
Housing Material	PET
Number of Contacts	37
Strain Relief	Yes
Dimensions	53.1 x 73 x 16.3 mm
Operating Temperature Range	-20 to +75°C
Standards Met	UL 94V-0