



Datasheet

Stock No: 313-2122

ENGLISH

RS Pro DC Motor Controller, Potentiometer, Voltage Control, 10 → 35 V, 2.2 A



Product Details:

4-Quadrant Module

This module is a 4-quadrant, linear output driver which is suitable for driving small dc. motors and gear motors up to 60 watts.

- Only single polarity voltage supply is required to achieve bi-directional motor speed control
- Employs armature feedback technique to maintain speed regulation
- Adjustable current limit facility
- Short circuit protection
- Speed control by external or internal potentiometer, or dc. control voltage
- Inbuilt thermal protection



Specifications:

Supply Voltage:	10 → 35 V
Current Rating:	2.2 A
Voltage Rating:	27.5 V
Compatible Motor Type:	Linear Output Motor
Control Input:	Potentiometer, Voltage
Length:	133.5mm
Width:	54mm
Depth:	20mm
Dimensions:	133.5 x 54 x 20 mm

