



Residual-current circuit-breaker



Powering Business Worldwide™

Part no. PXF-25/4/003-A

Article no. 236772

Technical data ETIM 4.0

Protection type (IP)			IP20
Short-time delayed type			false
Width in space units			4
Size (according to DIN 43880)			1
Impulse withstand current		kA	0.25 kA
Rated switching capacity		kA	0.5 kA
Short-circuit strength (Icw)		kA	10 kA
Selective type			false
Fault current type			A
Rated fault current		A	0.03 A
Number of poles			4
Rated voltage		V	400 V
Rated current		A	25 A
Mounting depth		mm	69.5 mm
Frequency		Hz	50 Hz
Mounting type			DIN-rail (DRA)
Additional equipment possible			true