

Entire Work Jacket with 2-way stretch

sorona® REPREVE

OEKO
TEX®
STANDARD
100
976-18801
DTI



Size: XS-S-M-L-XL-2XL-3XL-4XL-5XL-6XL
Shell fabric: 44% Elastomultiester / 36% Polyester (recycled) / 20% Cotton, 255 g/m²
Wash:

This work jacket is designed to combine functionality, durability, and comfort, making it ideal for demanding work conditions. It is made of Ripstop fabric with 2-way stretch, ensuring both flexibility and abrasion resistance. The concealed front zipper and a narrow placket protect against scratches. The jacket features many practical pockets, such as a spacious chest pocket with zipper and two side pockets, which also have zipper closures for secure storage. To ensure an optimal fit, the jacket has elastic and velcro adjustments at the sleeve openings, allowing for individual customization. Reflective print on both sleeves and back increases visibility. The extended back piece provides extra protection for the lower back, which is advantageous in cold or windy environments. A D-ring in the right pocket makes it easy to attach ID cards, for example. The jacket has ample space for company

- Made of Ripstop with 2-way stretch for increased durability and flexibility
- Concealed front zipper with narrow placket closure to avoid scratches
- Spacious chest pocket with zipper
- Two side pockets with zipper for safe storage
- Elastic and Velcro at the bottom of the sleeves for better fit and comfort
- Reflective print on the sleeves and back for increased visibility
- Extended back piece for protection of the lower back
- Ample room for company profiling
- D-ring in the right pocket for easy attachment of ID card

ENGEL®