

# Pneum. contact metal OD 6 male



Part number	09 14 000 6356
Specification	Pneum. contact metal OD 6 male
HARTING eCatalogue	https://b2b.harting.com/09140006356

#### Identification

Category	Contacts
Type of contact	Pneumatic contact
Description of the contact	Without shut-off
	Straight

#### Version

Gender
--------

#### Technical characteristics

Limiting temperature	-20 +85 °C
Operating pressure	≤10 bar
Tube outer diameter	6 mm

## Material properties

Material (contacts)	Brass
Material (seal)	NBR
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes



## Material properties

REACH SVHC substances Lead

## Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076
	CSA-C22.2 No. 182.3 ECBT8.E235076

#### Commercial data

Packaging size	10
Net weight	15.3 g
Country of origin	Germany
European customs tariff number	39269097
eCl@ss	27440204 Contact for industrial connectors