



Part Number : [192030083](#)
Product Description : Krimptite Temp-Term Ring
Tongue Terminal for 16-14 AWG Wire, Stud Size 8 (M4)
Series Number : 19203
Status : Active
Product Category : Ring and Spade Terminals
Engineering Number : BB-U-137-08



Documents & Resources

Drawings
[192030083 sd.pdf](#)
Specifications
[PS-19902-013-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Ring and Spade Terminals
Series	19203
Description	Krimptite Temp-Term Ring Tongue Terminal for 16-14 AWG Wire, Stud Size 8 (M4)
Comments	1200° F (649° C)
Keyword	Ring Terminal, Ring Terminals
Product Name	Krimptite,Temp-Terms
Type	Ring
UPC	800755059397

Agency

UL	E32244
----	--------

Physical

Barrel Type	Closed
Insulation	None
Net Weight	0.628/g
Packaging Type	Bag
Stud Size	8 (M4)
Wire Size (AWG)	14, 16
Wire Size mm²	1.00-2.50

Application Tooling

Global

Description	Part Number
PremiumGrade Hand Crimp Tool for Krimptite/Versakrimp Terminals and Splices, 22-10 AWG and 6.0mm ² - 0.5mm ²	<u>640030100</u>
Crimp Head for the AT-200 Pneumatic Hand Tool	<u>640070100</u>
ServiceGrade Hand Crimp Tool - Ratchet	<u>640160038</u>