

**S-20 ; 0...250 bar gauge; 0 ... 10 V, 3-wire @ DC 12...35 V**

**S-20 ; 0...250 bar gauge; 0 ... 10 V, 3-wire @ DC 12...35 V**

Item number: 14071210

Quantity: 1 pcs.

Order code: S-20-3-BG525-HSC3K-F-AGGZZZ-ZWZ W1011S20Z-ZZZZ21Z3-SS1CLZ3APSZZE-ZZGDZZSAZZZS1

Overview: S-20 ; 0...250 bar gauge; 0 ... 10 V, 3-wire @ DC 12...35 V  
Pressure transmitter Model S-20  
Non-linearity: 0.25% BFSL  
Overpressure limit: 2 times  
Process connection: G 1/2 B EN 837 ; Sealing: copper  
Pressure port: D 2.5 mm  
Electrical connection: angular connector DIN 175301-803 A mating connector included  
pin assignment el. connection: U+=1, U-=2, S+=3  
Permissible medium temperature: -30...+100°C  
shock and vibration resistance: 100 g shock, 20 g vibration  
Approvals: cULus  
Test protocol: with test protocol

Details: S-20 ; 0...250 bar gauge; 0 ... 10 V, 3-wire @ DC 12...35 V  
Pressure transmitter Model S-20  
Non-linearity: 0.25% BFSL  
Overpressure limit: 2 times  
Process connection: G 1/2 B EN 837 ; Sealing: copper  
Pressure port: D 2.5 mm  
Electrical connection: angular connector DIN 175301-803 A mating connector included  
pin assignment el. connection: U+=1, U-=2, S+=3  
Permissible medium temperature: -30...+100°C  
shock and vibration resistance: 100 g shock, 20 g vibration  
Approvals: cULus  
Test protocol: with test protocol