

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [5013311327](#)
Status: **Active**
Overview: Pico-Clasp Wire-to-Board Connectors
Description: 1.00mm Pitch, Pico-Clasp PCB Header, Single Row, Vertical, Surface Mount, Tin Plated, Inner Positive Lock, 13 Circuits, Red

Documents:

Drawing (PDF)	Application Specification 5013300000-AS-000 (PDF)
Product Specification 5013300000-PS-001 (PDF)	Packaging Specification SPK-501331-002-001 (PDF)
Product Specification 5013301000-PS-001 (PDF)	RoHS Certificate of Compliance (PDF)



Agency Certification

UL E29179

General

Product Family	PCB Headers
Series	501331
Application	Signal, Wire-to-Board
Overview	Pico-Clasp Wire-to-Board Connectors
Product Name	Pico-Clasp
Taxonomy	PCB Headers and Receptacles
UPC	800756914671

Physical

Breakaway	No
Circuits (Loaded)	13
Circuits (maximum)	13
Color - Resin	Red
Durability (mating cycles max)	30
First Mate / Last Break	No
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	254.800/mg
Number of Rows	1
Orientation	Vertical
PCB Locator	No
PCB Retention	Yes
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	1.00mm
Polarized to Mating Part	Yes
Polarized to PCB	No
Shrouded	Fully
Stackable	No
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	Surface Mount

Electrical

Current - Maximum per Contact	1.0A
Voltage - Maximum	100V AC (RMS)/DC

Material Info

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[501331](#) Series

Mates With

[501330](#) Pico-Clasp Wire-to-Board Female Housing

Reference - Drawing Numbers

Application Specification	5013300000-AS-000
Packaging Specification	SPK-501331-002-001
Product Specification	5013300000-PS-001, 5013301000-PS-001
Sales Drawing	SD-501331-002-001, SD-501331-002-002, SD-501331-004-001, SD-501331-004-002, SD-501331-004-003

This document was generated on 09/05/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION