

Universe	Professional
Type	Verticality
Category	Harnesses
Subcategory	Fall arrest harnesses



HI-VIZ vest for NEWTON harnesses

Fluorescent-colored vest with reflective strips makes the worker highly visible in all lighting conditions. It installs quickly and easily on NEWTON, NEWTON FAST and NEWTON EASYFIT harnesses. The sternal buckle, the multiple attachment points and the connector-holders all remain accessible for optimal freedom of movement.



The sternal buckle, the sternal and dorsal attachment points and the connector-holders all remain accessible when the vest is installed on the harness.

Short Description High visibility vest for NEWTON harnesses

Selling Points



- Fluorescent-colored vest with reflective strips makes the worker highly visible. The harness thus allows the worker to be seen more easily on a work site, road, or industrial site, in all lighting conditions.
- Quick and easy setup:
 - quick and easy to install and remove
 - FAST LT PLUS sternal buckle, sternal and dorsal attachment points, and the connector-holders all remain accessible when the vest is installed.
 - zipper on the back for ventilation
 - compatible with NEWTON, NEWTON FAST and NEWTON EASYFIT (1) harnesses
- Two zippered pockets for stowing small items
- Machine washable up to 30° C
- Available in two colors: yellow and orange

(1) Versions starting in 2021.

Specification

- Weight: 380g
 - Material(s): nylon
-

Specifications by reference

Reference(s)	C073GA00	C073HA00
		
Color(s)	yellow	orange
Made in	CN	CN
Guarantee	3 years	3 years
Inner pack count	1	1
Case quantity	11	11
EAN	3342540836549	3342540836556

Related product(s)

- NEWTON European version
- NEWTON international version
- NEWTON FAST European version
- NEWTON FAST international version
- NEWTON EASYFIT European version
- NEWTON EASYFIT international version