

Product Information



12981101014P80

EAN 4031582300024

Fixed castor, Fork made of pressed steel, bright zinc plated, blue passivated, axle riveted, Plate, round.
Wheel centre made of Polyamide, plain bearing

Technical Data

Wheel diameter	14 mm
Width of Tread	14 mm
Castor width	0 mm
Size of Plate	26 mm
Plate hole centres	20 mm
Plate hole	2.5 mm
Overall height	13.5 mm
Temperature	-20 / + 60 °C
Standard	EN 12528
Weight	0.008 kg
Hardness of tread	D 65 Shore
Load capacity	15 kg
Load capacity (static)	30 kg

Roll performance	+	+	+	+	+
Movement noise	+	+	+	+	+
Attrition	+	+	+	+	+
Corrosion resistance	+	+	+	+	+

