

Han 1A-back shell 5,7-10mm



Part number	09 10 000 0400
Specification	Han 1A-back shell 5,7-10mm
HARTING eCatalogue	https://b2b.harting.com/09100000400

Identification

Category	Hoods/Housings
Series	Han [®] 1 A
Type of hood/housing	Cable adapter

Version

Size	1 A
Version	Top entry
Cable entry	1x Integrated

Technical characteristics

Limiting temperature	-30 ... +90 °C
Number of relockings	<10
Degree of protection acc. to IEC 60529	IP65
Cable diameter	5.7 ... 10 mm

Material properties

Material (hood/housing)	Polyamide
Colour (hood/housing)	RAL 9005 (jet black)
Material (seal)	TPE
Colour (seal)	Yellow
Material flammability class acc. to UL 94	V-0

Specifications and approvals

Specifications	EN 45545-2 R22: HL1, HL2, HL3 EN 45545-2 R23: HL1, HL2, HL3
----------------	--



Pushing Performance

Specifications and approvals

	EN 45545-2 R24: HL1, HL2, HL3 EN 61373 Cat 1B
Approvals	DNV GL

Commercial data

Packaging size	1
Net weight	10.25 g
Country of origin	Germany
European customs tariff number	85366990
eCl@ss	27440202 Shell for industrial connectors