

Technical Characteristics

Bezel Material	Chromium Plated Metal
Button/Cap Color	Green-Red
Ampere Rating	10A
Approvals	UL Listed File Number E42259 CCN NKCR - CSA Certified File Number LR25490 Class 3211 03 - CE Marked
Button Type	Standard
Catalog Reference Number	9001CT0001
Contact Configuration	1 N.O./1 N.C.
Contact Material	Silver Alloy
Enclosure Type	Water tight, Dust tight, Oil tight and Corrosion Resistant (Indoor/Outdoor)
Enclosure Rating	NEMA 4/4X/13; IP65
Head Type	Square
Markings	START/STOP
Maximum Voltage Rating	600V
Mounting Type	Panel
Mounting Position	All
Number of Operators	2
Operator Action	(2) Maintained (with interlock)
Operator Type	Non-Illuminated
Terminal Type	Screw Clamp
Size	30mm
Utilization Category	AC15 - DC13
Type	KX

Shipping and Ordering

Category	21427 - Push Buttons, 30 mm, Square, Type KX
Discount Schedule	CP1
Article Number	785901524519
Package Quantity	1
Weight	0.39 lbs.
Availability Code	Stock Item: This item is normally stocked in our distribution facility.
Returnability	Y

As standards, specifications, and designs change from time to time, please ask for confirmation of the information given in this document.