

SAC-4P-30,0-28X/M12FS SH OD - Sensor/actuator cable



1408855

<https://www.phoenixcontact.com/in/products/1408855>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 4-position, PE-X/PE-X halogen-free, black-gray RAL 7021, shielded, free cable end, on Socket straight M12, coding: A, cable length: 30 m, for outdoor applications, with high-grade steel knurl

Your advantages

- Easy and safe: 100 % electrically tested plug-in components
- Robust throughout: resistant to oil, UV, and ozone, withstands temperatures from -40°C ... +105°C
- Reliable signal transmission – 360° shielding in environments with electromagnetic interference

Commercial data

Item number	1408855
Packing unit	1 pc
Minimum order quantity	20 pc
Note	Made to order (non-returnable)
Sales key	BF1
Product key	AF1CJA
GTIN	4046356835015
Weight per piece (including packing)	2,171 g
Weight per piece (excluding packing)	2,171 g
Customs tariff number	85444290
Country of origin	PL

SAC-4P-30,0-28X/M12FS SH OD - Sensor/actuator cable



1408855

<https://www.phoenixcontact.com/in/products/1408855>

Technical data

Product properties

Product type	Sensor/actuator cable
Application	External areas
Number of positions	4
No. of cable outlets	1
Shielded	yes
Coding	A

Insulation characteristics

Degree of pollution	3
---------------------	---

Material specifications

Flammability rating according to UL 94	V0
Seal material	FPM
Material of grip body	PP
Contact material	CuSn
Contact surface material	Ni/Au
Contact carrier material	PP
Material for screw connection	Stainless steel

Electrical properties

Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage U_N	48 V AC
	60 V DC
Nominal current I_N	4 A

Signaling

Status display	no
Status display present	No

Connector

Connection 1

Type	free cable end
------	----------------

Connection 2

Type	Socket straight M12
Number of positions	4
Coding type	A

Cable/line

Cable length	30 m
--------------	------


PE-X black [28X]

SAC-4P-30,0-28X/M12FS SH OD - Sensor/actuator cable



1408855

<https://www.phoenixcontact.com/in/products/1408855>

Dimensional drawing	
Cable weight	74 kg/km
Number of positions	4
Shielded	yes
Cable type	PE-X black [28X]
Conductor structure signal line	28x 0.15 mm
AWG signal line	20
Conductor cross section	4x 0.5 mm ² (Signal line)
Wire diameter incl. insulation	1.6 mm ±0.05 mm (Signal line)
External cable diameter	6.80 mm ±0.2 mm
Outer sheath, material	PE-X
External sheath, color	black-gray RAL 7021
Conductor material	Bare Cu litz wires
Material wire insulation	PE-X
Single wire, color	brown, white, blue, black
Thickness, insulation	approx. 0.30 mm (Core insulation) approx. 0.70 mm (Outer cable sheath) approx. 0.45 mm (Inner sheath)
Overall twist	4 wires, twisted
Length of twist, overall twist	108.8 mm
Optical shield covering	85 %
Max. conductor resistance	≤ 39 Ω/km (at 20 °C)
Insulation resistance	≥ 100 MΩ*km (at 20 °C)
Cable capacity	≤ 100 nF/km (Conductor-conductor, asymmetrical/touching) ≤ 85 nF/km (Conductor-conductor, symmetrical/star quad) ≤ 150 nF/km (Wire/shield)
Nominal voltage, cable	≤ 300 V AC
Test voltage	≥ 3000 V AC
Smallest bending radius, fixed installation	34 mm
Smallest bending radius, movable installation	68 mm
Dynamic load capacity (bending)	Max. bending cycles: 1000000, Bending radius: 68 mm, Traversing path: 10 m, Traversing rate: 3 m/s, Acceleration: 10 m/s ²
Halogen-free	in accordance with DIN VDE 0472 part 815
Flame resistance	according to DIN 60332-1-2 according to DIN EN 50266-2-5
Resistance to oil	in accordance with DIN EN 60811-2-1

SAC-4P-30,0-28X/M12FS SH OD - Sensor/actuator cable



1408855

<https://www.phoenixcontact.com/in/products/1408855>

Other resistance	UV resistant (according to DIN VDE 0276-605)
Special properties	Irradiated
Ambient temperature (operation)	-40 °C ... 105 °C (cable, fixed installation)
	-15 °C ... 105 °C (Cable, flexible installation)

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65
	IP68
Ambient temperature (operation)	-40 °C ... 105 °C (Plug / socket)
	-40 °C ... 85 °C (On sudden changes in temperature (according to IEC 60512-11-4))

Standards and regulations

M12

Standard designation	M12 connector
Standards/specifications	IEC 61076-2-101


SAC-4P-30,0-28X/M12FS SH OD - Sensor/actuator cable

1408855

<https://www.phoenixcontact.com/in/products/1408855>

Drawings

Schematic diagram



Pin assignment M12 socket, 4-pos., A-coded, view female side


SAC-4P-30,0-28X/M12FS SH OD - Sensor/actuator cable



1408855


<https://www.phoenixcontact.com/in/products/1408855>

Circuit diagram



Contact assignment of the M12 socket

Dimensional drawing



M12 x 1 socket, straight

SAC-4P-30,0-28X/M12FS SH OD - Sensor/actuator cable



1408855

<https://www.phoenixcontact.com/in/products/1408855>

Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/in/products/1408855>

DNV

Approval ID: TAE00002K4

SAC-4P-30,0-28X/M12FS SH OD - Sensor/actuator cable



1408855

<https://www.phoenixcontact.com/in/products/1408855>

Classifications

ECLASS

ECLASS-11.0	27060311
ECLASS-12.0	27060311
ECLASS-13.0	27060311

ETIM

ETIM 9.0	EC001855
----------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

SAC-4P-30,0-28X/M12FS SH OD - Sensor/actuator cable



1408855
<https://www.phoenixcontact.com/in/products/1408855>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

SAC-4P-30,0-28X/M12FS SH OD - Sensor/actuator cable



1408855

<https://www.phoenixcontact.com/in/products/1408855>

Accessories

SACC-M12MS-5CON-DM 5-8 SH VA - Connector

1440025

<https://www.phoenixcontact.com/in/products/1440025>



Connector, 5-position, shielded, Plug straight M12, coding: A, Screw connection, knurl material: Stainless steel 1.4404, cable gland M16, external cable diameter 5.5 mm ... 8.6 mm

TSD 04 SAC - Torque screwdriver

1208429

<https://www.phoenixcontact.com/in/products/1208429>



Torque screwdriver, with preset torque of 0.4 Nm and 4 mm hexagonal drive for M12 connectors

SAC-4P-30,0-28X/M12FS SH OD - Sensor/actuator cable



1408855

<https://www.phoenixcontact.com/in/products/1408855>

TSD-M 1,2NM - Torque screwdriver

1212224

<https://www.phoenixcontact.com/in/products/1212224>



Torque screw driver, accuracy as per EN ISO 6789 standard, adjustable from 0.3 - 1.2 Nm

TSD-M SAC-BIT ADAPTER - Adapter insert

1212600

<https://www.phoenixcontact.com/in/products/1212600>



Adapter bit for TSD-M...torque tools, E6.3-1/4" drive with 4 mm hexagon to accommodate SAC bits

SAC-4P-30,0-28X/M12FS SH OD - Sensor/actuator cable



1408855

<https://www.phoenixcontact.com/in/products/1408855>

SAC BIT M12-W14 - Tool

1212513

<https://www.phoenixcontact.com/in/products/1212513>



Nut for assembling sensor/actuator cables with M12 connector and M12 connectors for assembly, with a hexagonal knurl wrench size of 14 mm, with 4 mm hexagonal drive

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.

A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420

info@phoenixcontact.co.in