



### Main

Range of product	Thorsman
Product name	Goliath 250
Product or component type	Work lamp
Light source	Compact fluorescent tube 55 W

### Complementary

Type of installation	Outdoor Indoor
[Ue] rated operational voltage	230...240 V
Plug pole configuration	2P
Plug standard	European
Light source type	Glare-proof Flicker-proof
Luminous flux	4000 lm
Bulb lifespan	8000 h
Colour rendering index	R <sub>a</sub> =82
Colour temperature	3500 K
Illuminance	3 m : 210 lux 1 m : 1890 lux
Cable insulation material	Neoprene
Housing material	PC + rubber
Electrical connection	5 m H07RN-F2x1.0 feed power cord
Electrical insulation class	Class II
Marking	F ENEC 14
Height	316 mm
Width	316 mm
Depth	91 mm
Product weight	2.9 kg

### Environment

Environmental characteristic	Waterproof Dustproof
IP degree of protection	IP65
Quality labels	CE ENEC
Ambient air temperature for operation	-15...50 °C

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.