

SERVICE-MANOSKOP® torque wrench

730R Quick



Product no. **96504020**
GTIN **4018754269518**
Model **730R/20 QUICK**



Label.

SERVICE-MANOSKOP torque wrench 730R Quick 40-200N·m 1/2" L. 530mm

Properties.

- clicking type with dual stop signal
- no reset to "0" required, as the measuring element is only under load when a force is applied
- mount for interchangeable insert tools
- with QuickRelease safety lock
- Quick adjustment thanks to easy-to-operate locking lever in handle
- non-slip adjuster with thumb recess for quick torque adjustment
- double scale N·m/ft·lb or N·m/in·lb
- also available on request as a N·m only version without dual scale
- counter-clockwise tightening by turning the insert tools over
- clicking mechanism insensitive to continuous loads and counter-loads (up to the max. measurement range of the torque wrench)
- optimal calibration with perfectControl® calibration systems No. 7794 or calibration systems No. 7706, 7791
- easy adjustment without disassembly via 2 external adjustment screws
- with 2-component handle
- calibration certificate in accordance with DIN EN ISO 6789-2:2017
- **accuracy ± 4%**

Product highlights.



Rapid adjustment.


Easy and quick adjustment of the torque is carried out by an easy-to-operate clamping lever in the handle. The scale can be moved quickly and safely with an ergonomically shaped, non-slip adjustment element with thumb recess.

Adjustment does not require disassembly.

Quick adjustment from outside, no disassembly of the torque wrench required, with 2 adjustment points for the maximum & minimum values.





Technologies and features.



Low-wear bending beam system

Our torque wrench is equipped with a low-wear release system with a bending beam. Unlike conventional torque wrenches with coiled springs, the bending beam is not subjected to any load until the tool is in operation, which means that the spring does not need to be reset to '0' after use.

Technical drawing.



Technical attributes.

Scale division N·m	5 N·m
Measuring range N·m	40-200 N·m
Measuring range ft·lb	30-145 ft·lb
External square drive (inch)	1/2
b1	55 mm

Logistics data.

Depth mm (IFS)	530
Width mm (IFS)	55
Height mm (IFS)	55
WEEE/ElektroG	nicht ear-pflichtig
Length (packaged, mm)	530
Width (packaged, mm)	55

b2	43 mm	Height (packaging, mm)	55
DIN	DIN EN ISO 6789-2:2017	Volume (packaged, dm³)	1.60325 dm ³
Size	20	Product no.	96504020
Tool holder size [internal square]	14 x 18 mm	Weight (gross, kg)	1,640
Height mm (h)	55 mm	Weight PAP (kg)	0,000
Length mm (L)	530 mm	Weight PVC (kg)	0,066
LF	435 mm	GTIN	4018754269518
SF	25 mm	Country of origin AWR	GERMANY
		Region of origin	Nordrhein-Westfalen
		Customs tariff no.	82041100
		Packing standard	1
		Weight (g)	1626 g

Parts list.



50184020
MANOSKOP® torque
wrench

Variants.

Product no.	Model No. (ERP)	Description	GTIN
96501054	MANOSKOP® 730R/2-1 Quick	Service MANOSKOP® torque wrench 730R Quick 2-10N·m 1/4" L. 250mm	4018754339976
96504002	730R/2 QUICK	SERVICE-MANOSKOP torque wrench 730R Quick 4-20N·m 3/8" L. 255mm	4018754311354
96504004	730R/4 QUICK	Service MANOSKOP® torque wrench 730R Quick 8-40N·m 3/8" L. 285mm	4018754311361
96504005	730R/5 QUICK	SERVICE-MANOSKOP torque wrench 730R Quick 6-50N·m 3/8" L. 380mm	4018754269488
96504010	730R/10 QUICK	Service MANOSKOP® torque wrench 730R Quick 20-100N·m 1/2" L. 430mm	4018754269495
96504012	730R/12 QUICK	SERVICE-MANOSKOP torque wrench 730R Quick 25-130N·m 1/2" L. 475mm	4018754269501
96504020	730R/20 QUICK	SERVICE-MANOSKOP torque wrench 730R Quick 40-200N·m 1/2" L. 530mm	4018754269518
96504030	730R/30 QUICK	Service MANOSKOP® torque wrench 730R Quick 60-300N·m 1/2" L. 590mm	4018754326006

96504040	730R/40 QUICK	Service MANOSKOP® torque wrench 730R Quick 80-400N·m 3/4" L. 675mm	4018754269525
96504565	730RII/65 QUICK	Service MANOSKOP® torque wrench 730R Quick 130-650N·m 3/4" L. 1125mm	4018754269563

GTIN.



Images.



STAHLWILLE Eduard Wille GmbH

Lindenallee 27 · 42349 Wuppertal · Germany · Phone: +49 202 4791-0

info@stahlwille.de · www.stahlwille.com

© STAHLWILLE Eduard Wille GmbH, Wuppertal