

datasheet for BSB 20 K
article number: 930729102

product description:	order number: 930 729-102
description:	Multiple-spring wire plug with cable gland and 4 mm socket for onward connection capability. Screw connection up to maximum cable cross-section of 2.5 mm ² and external diameter of 4 mm. Nickel-plated brass contact material.
typ:	BSB 20 K blau/blue
system:	4mm system
order number:	930 729-102
color	
other color versions:	
technical data	
measurement category acc. to IEC 61010:	CAT I
pin dimensions	4 mm
type of contact:	pin (spring loaded)
type of termination:	screw
rated voltage:	30 VAC / 60 VDC
rated current: Please consider derating curve!	30 A
contact resistance:	3 mOhm
material	
contact material:	brass
contact surface material:	nickel
housing material:	PP
environmental conditions:	
temperature range:	-25 °C to +100 °C
flammable class:	
housing (basic material):	UL 94 HB
drawing	