

Mini Touch Key Constant Voltage Dimming Controller



- Ultra slim design
- Over temperature, overload and short circuit protections
- Auto Recall Function
- Easy 'Plug and Play' technology
- Wide 5 ~ 24VDC input range
- Reverse Polarity Protection
- Small compact design



Specification

Model Number	PDMINI
Voltage	5 ~ 24VDC
Rated Output Current	5A
Control Mode	Three press buttons
PWM Control	256 levels
PWM Frquency	1Khz
Components & PCB	SMD parts / Double sided FR-4 pcb
Working Temperature	-30 ~ 70°C
Power Connection	AWG 18 Red / Black cable
LED Connection	AWG 18 Red / Black cable
Cable Length	110mm
Weight	7.2g
Dimensions	33 x 12 x 5mm

FUNCTIONS

Brightness Levels	256 Levels
Dynamic Mode	7 Modes
Dynamic Speed Levels	10 Levels
Brightness Level	10 Levels
Brightness Adjustment	Up/Down
Max Brightness Shortcut	Yes
On/Off Operation	Yes

Mechanical Diagrams

