



Passive Components > Resistors > Surface Mount Resistors > SMD Power Resistor: 3 Watt, 1% Tol



Resistance Value: 910K Ω
Resistor Type: Power Resistor
Element Type: Thick Film
Package Size Code: 2512
Power Rating: 3 W

[All SMD Power Resistor: 3 Watt, 1% Tol \(140\)](#)

Features

Product Type Features

Resistor Type	Power Resistor
Element Type	Thick Film
Package Size Code	2512

Configuration Features

Number of Resistors	1
---------------------	---

Electrical Characteristics

Resistance Value	910K Ω
Power Rating	3 W
Resistance Class	1k Ω – 1M Ω
Passive Component Tolerance	1 %

Termination Features

Surface Mount Resistor Termination Type	Solder
---	--------



Number of Terminations	2
------------------------	---

Dimensions

Product Height	1.1 mm[.043 in]
Product Length	6.35 mm[.25 in]
Product Width	3.2 mm[.126 in]

Usage Conditions

Temperature Coefficient	±100 ppm/°C
-------------------------	-------------

Packaging Features

Packaging Method	Taped & Reeled
------------------	----------------

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

3522910KFT

910K ohm, Surface Mount Power Resistor, Thick Film, 2512, 3 W, 1 %, ±100 ppm/°C, Solder, 2 Terminations, 1.1 mm [.043 in] Height, CGS 3522



TE Part # CAT-C339-A76B

SMD Power Resistor: 3 Watt, 1% Tol

TE Part # 4-2176230-2

3522 2K2 5% 3W

Also in the Series | CGS 3522

Surface Mount Resistors(211)

Customers Also Bought

TE Part #5-2316114-6

2MM,REC,CNT,CRIMP,28-30AWG,0.76 UM,LP

TE Part #284415-8

TERMI-BLOK 900 PCB 8 POS. 3,81

TE Part #NB-PTCO-166

Pt100, 2.0x5.0, Class C, PTFD101C1A0

TE Part #1623804-3

SOQ10 3R9 5% WIRE

TE Part #EN3750-475

TCTL-1-5/16-U

TE Part #1217072-1

CONT AMVAR 125 BLADE 020 TPBR

TE Part #T4151210004-003

RPC-M12-MR-4CON-PVC-1.5

TE Part #1-1659250-0

H25734/R8000

TE Part #1558666-6

T9GS1L14-22

TE Part #1-2319848-6

END STACK DIP 6P J RECESS TUBE

3522910KFT

910K ohm, Surface Mount Power Resistor, Thick Film, 2512, 3 W, 1 %, ±100 ppm/°C, Solder, 2 Terminations, 1.1 mm [.043 in] Height, CGS 3522



Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2-2176232-1_BA.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2-2176232-1_BA.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2-2176232-1_BA.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

SMD POWER RESISTORS - TYPE 3522 SERIES

English