

Har-speed M12 malecont. Crimp AWG 23-26



Image is for illustration purposes only. Please refer to product description.

Part number	21 01 100 9019
Specification	Har-speed M12 malecont. Crimp AWG 23-26
HARTING eCatalogue	https://b2b.harting.com/21011009019

Identification

Category	Contacts
Series	har-speed
Type of contact	Crimp contact

Version

Gender	Male
Manufacturing process	Turned contacts
Performance level	1

Technical characteristics

Conductor cross-section	0.13 ... 0.25 mm ²
Conductor cross-section	AWG 26 ... AWG 23

Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Gold plated
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes



Pushing Performance

Material properties

REACH SVHC substances	Lead
-----------------------	------

Commercial data

Packaging size	100
Net weight	0.1 g
Country of origin	Switzerland
European customs tariff number	85369010
eCl@ss	27440204 Contact for industrial connectors