



230mm x 14 Tpi - 5 pc

METAL: THIN KERF BLADES

- Improved tooth geometry for best speed and double the lifetime.
- Bi-metal quality cutting teeth with 8% cobalt giving the ultimate in performance and lifetime.
- TOUGH NECK™: Stamped indentations around the reception strengthens the blade at its weakest point.
- Slim 0.90 mm thick blade body optimised for maximum speed and flexibility.



Article Number	48475187
Blade length (mm)	230
Max. cutting capacity metal pipe (mm)	10 - 175
Max. cutting capacity non-ferrous metals (mm)	3 - 11
Max. cutting capacity stainless steel (mm)	3 - 7
Max. cutting capacity steel (mm)	3 - 11
Pack quantity	5
Ref. No.	S1122BF