


FEATURES

- Density of 1.5 g/cm³
- Length of 1 m
- Width of 600 mm
- Thickness of 3 mm
- Suitable for use with water, acids and alkalis as well as ethylene glycol
- Natural rubber sheet with polyester insert in the centre for additional strength
- Minimum operating temperature of -20 °C
- Maximum operating temperature of +70 °C

RS PRO Black Rubber Sheet, 1m x 600mm x 3mm

RS Stock No.: 506-3090



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.



Product Description

For a versatile general-purpose barrier, turn to these natural rubber sheets. Natural rubber can withstand high temperatures of +70°C and lows of -20°C. These sheets can be used with water and ethylene glycol, as well as acids and alkalis, making them suitable for factory, workshop and manufacturing environments.

General Specifications

Colour	Black
Suitability	Cold Water, Ethylene Glycol, Hot Water
Finish	Smooth
Material	Natural
Application	Indoor use

Mechanical Specifications

Length	1000mm
Thickness	3mm
Width	600mm
Density	1.5g/cm ³

Operation Environment Specifications

Maximum Operating Temperature	+70°C
Minimum Operating Temperature	-20°C

Approvals

Compliance/Certifications	RoHS