

Eaton 248880

Catalog Number: 248880

Z-DSV-LLL.N. Rotary switches, L+N voltmeter, L1 - N3...

General specifications



Product Name
Eaton Distribution parts

EAN
4015082488802

Product Height
78.5 mm

Product Weight
0.12 kg

Catalog Number
248880

Product Length/Depth
65 mm

Product Width
52 mm

Compliances
RoHS conform

Product specifications

Equipment heat dissipation, current-dependent

3 W

Rated operational voltage (Ue) - max

690 V

Static heat dissipation, non-current-dependent

0 W

Voltage rating - min

440 V

Width in number of modular spacings

3

Number of poles

Single-pole

Color calotte

Other

Switch type

Other

Rated short-time withstand current (Icw)

10 kA

Lamp socket

Other

Ambient operating temperature - max

60 °C

Ambient operating temperature - min

-40 °C

Built-in depth

60 mm

Amperage rating

20 A

Voltage type

AC

Lamp type

Other

Degree of protection

IP20

Heat dissipation capacity

Resources

Declarations of conformity

[DA-DC-03_Z-DS](#)

Drawings

[eaton-wiring-diagram-z-ds-aufdr.jpg](#)

[eaton-dimensions-mas-ds3.jpg](#)

0 W

Heat dissipation per pole, current-dependent

0 W

Lamp power

0 W

Number of contacts (change-over contacts)

1

Number of contacts (normally closed contacts)

0

Number of contacts (normally open contacts)

0

Inscription

Other

Rated operational current for specified heat dissipation (In)

20 A

Rated Switching Capacity

0.02 kA



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia