



Part Number : [2262632063](#)
Product Description : Micro-Fit+ Versa Color Female-to-Pigtail Off-the-Shelf (OTS) Cable Assembly, Dual Row, 300.00mm Length, Tin (Sn) Plating, 6 Circuits, Natural (White)
Series Number : 226263
Status : Active
Product Category : Power and Signal Cable Assemblies




Documents & Resources

Drawings
[2262632063_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Power and Signal Cable Assemblies
Series	226263
Description	Micro-Fit+ Versa Color Female-to-Pigtail Off-the-Shelf (OTS) Cable Assembly, Dual Row, 300.00mm Length, Tin (Sn) Plating, 6 Circuits, Natural (White)
Application	Power, Wire-to-Board, Wire-to-Wire
Assembly Configuration	Single Ended Connector
Connector to Connector	Micro-Fit+ Versa Color-to-Pigtail
Product Name	Micro-Fit+ Versa Color
Type	Discrete Wire Assembly
UPC	198282213369

Electrical

Current - Maximum per Contact	13.0A
Voltage - Maximum	600V AC (RMS)/DC

Physical

Cable Length	300.00mm
Circuits (Loaded)	6
Circuits (maximum)	6
Color - Resin	Natural (White)
Gender	Female-Pigtail
Lock to Mating Part	Yes
Material - Metal	High Conductivity Copper
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	29.893/g
Number of Rows	2
Overmolded	No
Packaging Type	Bag

Pitch - Mating Interface	3.00mm
Plating min - Mating	2.500µm
Plating min - Termination	2.500µm
Single Ended	Yes
Termination Interface Style	Crimp or Compression
Wire/Cable Type	Discrete Wire, UL 1061
Wire Insulation Diameter	2.00mm
Wire Size (AWG)	16

Mates With / Use With

Mates with Part(s)

Description	Part Number
Micro-Fit+ Vertical, Dual Row, Through Hole Headers	<u>206832</u>
Micro-Fit+ Right-Angle, Dual Row, Through Hole Headers	<u>212528</u>
Micro-Fit+ Dual Row Surface Mount Headers	<u>218216</u>
Micro-Fit+ Versa Color Vertical, Dual Row, Through Hole Headers	<u>224246</u>
Micro-Fit+ Dual Row Plug Housings	<u>215922</u>