


Add-on-block 4P 25A 30mA AC



Technical Properties

Number of poles	4 P
Rated current	25 A
Rated residual operating current	30 mA
Residual current type	AC
Number of modules	3
Frequency	50 Hz
Rated operational voltage Ue	230/400 V
Operating temperature	-25 to 40 °C