

## Convenio

CONVENIO LINEAR SPOT 12V WH L400 KIT UK

0043321



### Range Features

- Convenio is a range of products that create a modular lighting system covering most of spot, linear and area lighting applications
- Unified electrical and mechanical interface allows the customer to create a variety of lighting schemes
- Contemporary and minimalist ultra slim design
- Seamless mounting brackets for easy installation
- Convenio Linear is a slim homogenous LED linear light used for undercabinet, wall and ceiling lighting applications
- Convenio Linear Spot light is used for wall washing or suspended table lamp applications
- Convenio Spot is a LED Spot light used for accent lighting with a high lumen output of 400lm
- Various accessories (flat corner, inside corner, outside corner, dimmable sensor switch) available for personalisation
- Available in warm white 3000K

## PRODUCT OVERVIEW

Beam angle(°)	25
Certifications	CE
Colour temperature (K)	3000
Colour	White/Silver
CRI (Ra)	80
EAN code	5410288433219
Luminous flux (lm)	600
Housing	Aluminium
IP rating	IP20
Light colour	Warm white
Mount	Surface mounted
Ordering number	0043321
Efficacy (Rated) (lm/w)	70
Average life (Rated) (h)	25000
Technology	LED
Voltage (V)	12 (220-240 input)
Included lamp	Integrated LED
Colour consistency (SDCM)	5 Step

## DATA TABLE

### General data

Average life (Nominal) (h)	25000
Certifications	CE
EAN code	5410288433219
Environment	Internal

## Convenio

CONVENIO LINEAR SPOT 12V WH L400 KIT UK

0043321

<b>General application</b>	Residential; Hospitality; Retail
<b>Housing</b>	Aluminium
<b>Mount</b>	Surface mounted
<b>Ordering number</b>	0043321
<b>Range features</b>	<p>Convenio is a range of products that create a modular lighting system covering most of spot, linear and area lighting applications</p> <p>Unified electrical and mechanical interface allows the customer to create a variety of lighting schemes</p> <p>Contemporary and minimalist ultra slim design</p> <p>Seamless mounting brackets for easy installation</p> <p>Convenio Linear is a slim homogenous LED linear light used for undercabinet, wall and ceiling lighting applications</p> <p>Convenio Linear Spot light is used for wall washing or suspended table lamp applications</p> <p>Convenio Spot is a LED Spot light used for accent lighting with a high lumen output of 400lm</p> <p>Various accessories (flat corner, Inside corner, outside corner, dimmable sensor switch) available for personalisation</p> <p>Available in warm white 3000K</p>
<b>Product name</b>	CONVENIO LINEAR SPOT 12V WH L400 KIT UK
<b>Average life (Rated) (h)</b>	25000
<b>Technology</b>	LED
<b>Product features</b>	LED linear spot striplight, 600LM, 8.5W, L400, 3000K, 3 x LED spots with 25 degree beam angle, includes driver and UK plug, white/silver aluminium body, low slimline profile, dimensions length 400mm, width 30mm, height 15mm, expandable with accessories, IP20.

### Optical data

<b>Beam angle(°)</b>	25
<b>Colour temperature (K)</b>	3000
<b>CRI (Ra)</b>	80
<b>Luminous flux (lm)</b>	600
<b>Light colour</b>	Warm white
<b>Colour consistency (SDCM)</b>	5 Step

### Physical data

<b>Colour</b>	White/Silver
<b>Height (mm)</b>	15
<b>IP rating</b>	IP20
<b>Lamp included</b>	Integrated
<b>Length (mm)</b>	400
<b>Width (mm)</b>	30
<b>Included lamp</b>	Integrated LED



## Convenio

CONVENIO LINEAR SPOT 12V WH L400 KIT UK

**0043321**



This luminaire contains built in LED lamps.

The lamps cannot be changed in the luminaire.





A++  
A+  
A  
~~B~~  
~~C~~  
~~D~~  
~~E~~  
~~F~~

LED



**SYLVANIA** 0043321 874/2012