

## RS Part Number: **795-2201** Specifications and dimensions



- Boxed Isolator 25 A DC 4 Pole
- 1000 V Rating for PV Applications
- Positive Snap Action Self Cleaning Contacts

| Features                                                               |                    |
|------------------------------------------------------------------------|--------------------|
| Height                                                                 | 170 mm             |
| Width                                                                  | 102 mm             |
| Depth                                                                  | 80 mm              |
| Depth including switch                                                 | 110 mm             |
| Degree of protection                                                   | IP65               |
| Standard                                                               | IEC 60364-7-712    |
| Maximum cable capacity                                                 | 16 mm <sup>2</sup> |
| <b>2 poles connected in series:</b>                                    |                    |
| Maximum switching current DC21 600V                                    | 25 A               |
| Maximum switching current DC21 800V                                    | 20 A               |
| Maximum switching current DC21 1000V                                   | 11 A               |
| <b>2 poles in parallel connected in series to 2 poles in parallel:</b> |                    |
| Maximum switching current DC21 600V                                    | 45 A               |
| Maximum switching current DC21 800V                                    | 20 A               |
| Maximum switching current DC21 1000V                                   | 11 A               |
| <b>4 poles connected in series:</b>                                    |                    |
| Maximum switching current DC21 600V                                    | 25 A               |
| Maximum switching current DC21 800V                                    | 25 A               |
| Maximum switching current DC21 1000V                                   | 25 A               |