

filter MS9-LF-G-EUV

Part number: 564107

FESTO

40 µm filter, metal bowl guard, fully automatic condensate drain, flow direction from left to right.



Data sheet

Feature	Value
Size	9
Series	MS
Assembly position	Vertical +/- 5°
Grade of filtration	40 µm
Condensate drain	fully automatic
Design structure	Sintered filter with centrifugal separator
Max. condensate volume	220 ml
Operating pressure	2 ... 12 bar
Operating medium	Compressed air to ISO 8573-1:2010 [7:9:-] Inert gases
Corrosion resistance classification CRC	2 - Moderate corrosion stress
Storage temperature	5 ... 60 °C
Air purity class at output	Compressed air in accordance with ISO8573-1:2010 [7:8:4]
Medium temperature	5 ... 60 °C
Ambient temperature	5 ... 60 °C
Product weight	2,000 g
Mounting type	Optional Line installation with accessories
Material of cover	PA-reinforced
Material of spin disc	POM
Material of filter holder	POM
Materials note	Conforms to RoHS
Material of connecting plate	Aluminium die cast
Material mounting bracket	Aluminium die cast
Material filter	PE
Material housing	Aluminium die cast
Material module connector	Aluminium die cast
Material bowl	Wrought Aluminium alloy
Material cup seal	NBR
Material screen	PA
Material separating plate	POM