

DCF891P2T-QW

18V XR Brushless 1/2" Hog Ring Anvil Impact Wrench - 2 X 5AH

The DCF891 18V XR Impact Wrench with Hog Ring Anvil was designed to easily handle various fastening projects. Get up to 812Nm of fastening torque and 1084Nm of max breakaway torque in a 175mm long body with this compact power tool that offers easy maneuverability without sacrificing power. Choose between 4 modes to allow for reliable high-level performance, operability, and versatility. Dark work areas are no problem with this Cordless Impact Wrench, which comes with an LED work light for visibility in dimly lit spaces.

Selling Propositions

- 812Nm of Fastening Torque
- Coppia di picco 1084Nm
- Compact 175mm Head Length
- Brushless Motor
- 4 Mode Switch for Accurate Application Control
- 1/2" Anvil with Hog Ring
- Supplied with 5Ah Battery Packs and Charger
- Shipped in TSAK

Standard Equipment

- TSTAK Kit Box (1)[fr]
- 2x XR 18V 5.0Ah Battery Packs
- Multi-Voltage Charger

Warranty specifications

- Dewalt 3 year european PT Guarantee

Specifications	
Max Torque	812.0 Nm
No Load Speed	0 - 2000
Impacts per Minute	0 - 3250 ipm
Max. Bolt Diameter	M24
No. of Modes	4.0
Anvil Size and Type	1/2" Hog Ring