

**306 27****Ring slogging spanner**

Code	ETIM
<b>6475190</b>	<b>EC002188</b>
EAN	UNSPSC
<b>4010886647516</b>	<b>27-11-17-05</b>
Country of origin	eCl@ss
<b>Germany</b>	<b>21-04-01-03</b>
Customs tariff number	
<b>82041100</b>	



### Article description

- Top-grade industrial quality for the hardest of continuous use
- For heavy-duty work
- Special sizes available on request up to 250 mm
- Up to length 435 mm made of chrome vanadium steel 31CrV3, from length 480 mm made of material C35
- \* not standardised
- Acc. to DIN 7444

### Article information

Contents [Qty of pieces]	<b>1</b>	Standard	<b>DIN 7444</b>
Net weight [kg]	<b>0,328 kg</b>	Width across flats 1 [mm]	<b>27</b>
Total length [mm]	<b>180 mm</b>	Head height 1 [mm]	<b>15,5 mm</b>
Surface	<b>oiled</b>	Width of head 1 [mm]	<b>47,0 mm</b>
Material	<b>31CrV3</b>	Ring profile	<b>UNIT-DRIVE</b>