












MARQUARDT

SERIES 3230 - SINGLE AND DOUBLE-POLE ROCKER SWITCHES

TO 10 (5) A 24 V DC

 Combination (rocker separate)	Voltage lamp in V	Housing color	10 (5)A 24 V 10E4		10 (5)A 12V 10E4		Connection type	Connection description	Miscellaneous	Stock version
			●		●					
Changeover switch snapping 2-step (SPDT)										
3230.0502			●					3.0 x 0.8	2 x single-pole changeover switch circuit symbol: 3.31	
3230.0501				●				3.0 x 0.8	2 x single-pole changeover switch circuit symbol: 3.31	
Changeover switch snapping 2-step with function indicator (SPDT)										
3230.0602			●					3.0 x 0.8	2 x single-pole changeover switch circuit symbol: 3.33	
3230.0601				●				3.0 x 0.8	2 x single-pole changeover switch circuit symbol: 3.33	
Changeover switch momentary 2-step (SPDT)										
3230.0702			●					3.0 x 0.8	2 x single-pole changeover switch circuit symbol: 3.32	
3230.0701				●				3.0 x 0.8	2 x single-pole changeover switch circuit symbol: 3.32	
Lamp										
Lamp (cap separate)	Voltage lamp in V	Housing color	10 (5)A 24 V 10E4		10 (5)A 12 V 10E4		Connection type	Connection description	Miscellaneous	Stock version
			●		●					
3237.0102	24 24							3.0 x 0.8	LED red / red	
3237.0104	24 24							3.0 x 0.8	LED red / green	
3237.0106	24 24							3.0 x 0.8	LED green / green	
3237.0108	24 24							3.0 x 0.8	LED yellow / green	