

# tesa® 50600



## Product Information

### Información Técnica: (valores promedio)

Los valores en esta sección son considerados solamente como representativos o típicos y no deben usarse para propósitos específicos.

#### Technical Data

• Material de soporte	PETP	• Elongación a la ruptura	110 %
• Espesor total	80 µm	• Resistencia a la rotura	75 N/cm
• Tipo de adhesivo	silicona	• Resistencia a la temperatura	220 °C

#### Adhesion to

- Adhesión sobre acero 4.0 N/cm

#### Properties

- |                                |      |                              |      |
|--------------------------------|------|------------------------------|------|
| • Se puede cortar con la mano. | ●    | • Color en el borde definido | ●●●● |
| • Fácil de quitar              | Si   | • Conformable                | ●●   |
| • Buen anclaje de la pintura   | ●●●● |                              |      |

Evaluation across relevant tesa® assortment: ●●●● very good ●●● good ●● medium ● low

#### Additional Information

tesa® 50600 también está disponible en un soporte de poliéster especial.

## Disclaimer

tesa® products prove their impressive quality day in, day out in demanding conditions and are regularly subjected to strict controls. All information and recommendations are provided to the best of our knowledge on the basis of our practical experience. Nevertheless tesa SE can make no warranties, express or implied, including, but not limited to any implied warranty of merchantability or fitness for a particular purpose. Therefore, the user is responsible for determining whether the tesa® product is fit for a particular purpose and suitable for the user's method of application. If you are in any doubt, our technical support staff will be glad to support you.



For latest information on this product please visit  
<http://l.tesa.com/?ip=50600>