

## 3SB3901-1UB WEDGE-BASE LED LAMP, DC 24V,

ACCESSORY / SPARE PART ROUND, 22MM/SQUARE,  
26X26MM: LED SUPER-BRIGHT LAMPS, WEDGE-BASE  
WEDGE-BASE W2 X 4.6D RATED VOLTAGE 24V AC/DC  
OPERATIONAL CURRENT 10 MA WHITE



### Certificates/approvals:

**General Product Approval**  
ROSTEST

**Test Certificates**  
Manufacturer

**other**  
Manufacturer

### Further information:

**Information- and Downloadcenter (Catalogs, Brochures,...)**  
<http://www.siemens.com/industrial-controls/catalogs>

**Industry Mall (Online ordering system)**  
<http://www.siemens.com/industrial-controls/mall>

**CAX-Online-Generator**  
<http://www.siemens.com/cax>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**  
<http://support.automation.siemens.com/WW/view/en/3SB3901-1UB/all>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)**  
[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=3SB3901-1UB](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3SB3901-1UB)

**last change:**