

## M12 Cable Assembly D-cod st/st m/m 4,5m



Image is for illustration purposes only. Please refer to product description.

Part number	21 34 929 2477 045
Specification	M12 Cable Assembly D-cod st/st m/m 4,5m
HARTING eCatalogue	<a href="https://harting.com/21349292477045">https://harting.com/21349292477045</a>

### Identification

Category	System cabling
Series	Circular connectors M12
Element	Cable assemblies
Specification	Pre-assembled on both sides
Connector 1	M12 D-coding Male Straight
Connector 2	M12 D-coding Male Straight
Type of cable	Copper cable (round)

### Version

Cable length	4.5 m
Number of cores	4
Core structure	4x AWG 22/7
Coding	D-coding

### Technical characteristics

Transmission characteristics	Cat. 5 Class D up to 100 MHz
Data rate	10 Mbit/s 100 Mbit/s
Limiting temperature	-25 ... +70 °C

### Material properties

Material (cable)	PUR (polyurethane)
------------------	--------------------



**Pushing Performance**  
Since 1945

## Material properties

Colour (cable) Green

---

## Specifications and approvals

Specifications	UN/ECE-R 118 fire protection for rolling stock
PROFINET	Yes

---

## Commercial data

Packaging size	1
Net weight	315.5 g
Country of origin	Czechia
European customs tariff number	85444290
GTIN	5713140247499
eCl@ss	27060390 Ready-made data cable (unspecified)
ETIM	EC002599
UNSPSC 24.0	26121600

---