



DW0811-XJ

DEWALT 360° LINE+1 VERTICAL BEAM LASER

Selling Proposition

- Simulates functionality of rotary laser
- Range : 10M-30M - Accuracy : +/- 4mm/10m
- Self leveling 360° line and vertical line - Projects bright crossing horizontal and vertical lines
- Vertical-Adjust Base - For easy set-up and fine tune adjustments
- 1/4" and 5/8" Thread Mounts - Thread Mounts For versatility
- Full-time pulse mode allows use with detector - Detector Maintains full brightness for visibility

Standard Equipment

- DEWALT 360° LINE+1 VERTICAL BEAM LASER

Warranty Specifications

- 1 Year Free Service Contract
- 30 Day Money Back Guarantee
- 1 Year Warranty

Specifications	
Laser class	1
Pøesnost	4mm/10m mm/m
Number of beams	
Direction of beams	
Indoor Visibility Range	30 m
Self-Levelling Range	4 °
Power Supply	3xAA
Tripod connection	YES