



BEE
THEFIRST

CREATIVITY THAT MATTERS

BEAUTY
IS ONLY
SKIN-DEEP.

**WE BEG
TO DIFFER.**

From its award-winning design to its unique portability and usability, BEETHEFIRST 3D printer offers a blend of features you won't find anywhere else.

Easy to use. Easy to transport. Easy to live with.

BEE THEFIRST

TECHNICAL SPECIFICATIONS

Printing technology
Max. printing volume

FFF
190mm x 135mm x 125mm
(7,48 x 5,31 x 4,92 in)
50 microns | 300 microns
1.75 mm

Layer resolution
Filament diameter

DIMENSIONS

Volume
Approx. Weight

40 x 40 x 14 cm (15,75 x 15,75 x 5,51 in)
9,5 kg (21 lb)

RECOMMENDED ENVIRONMENT

Working ambient temperature
Storage temperature
Humidity

15° - 30° C (59° - 86° F)
0° - 30° C (32° - 86° F)
Low

POWER SUPPLY (region specific)

AC Input 1
AC Input 2

100 - 120 VAC 3,0A 50 - 60 Hz
200 - 240 VAC 2,0A 50 - 60 Hz

CONNECTIVITY

USB

STRUCTURE

Exterior
Printing table

Metal / Acrylic
Polycarbonate

SOFTWARE

Name
File type

BEESOFT (Open Source)
.stl

MINIMUM SYSTEM REQUIREMENTS

Windows (7 / 8) | Linux (12.04 +)
Core i3 | AMD Phenom II | AMD Athlon X2
RAM: 2GB
Free disk space: 500 MB
Graphics card (GPU): 512 MB dedicated

Mac OS X (10.8/10.9+)
Mac hardware: late-2008+

Contact us:
sales@beeverycreative.com
partnership@beeverycreative.com