



## **DATASHEET:-**

**SIP Airmate OL197/10RC**

**ProTech Air Compressor**

SIP Part Number **06254**

### **Product Details:**

Direct Drive Compressor with Integrated Air Regulator

Single Cylinder Oil-Free Pump

Ideal for Nail & Stapling applications

Fitted with Tank & Outlet Pressure Gauges and air  
connector Small & Portable

### **Specification:**

Supply: 230v 50Hz

Motor: 1.5HP (1.1KW)

Air Receiver: 10 Ltrs

Piston Displacement: 8 CFM

Free Air Delivered (FAD): 4 CFM

Max Air Pressure: 10 bar (145psi)

Noise: 97 dB(A)

Net weight: 11KG

Packaged Dimensions: 315 x 475 x 535mm

1 Year Warranty