



Main

Range of product	Modicon M171
Product or component type	Communication module
Communication port protocol	BACnet IP SMTP HTTP Ethernet Modbus TCP Modbus RTU RS485 BACnet MS/TP

Complementary

Integrated connection type	Ethernet RJ45 - twisted pair RS485 wire crimp - twisted pair
Adjustment	Pitch 3.81 mm
Electrical connection	Removable screw terminal block
Physical interface	90° insertion - 2.5 mm ² cable RJ45
Supply	Via base board EVD/EVC
Product compatibility	Logic controller M171 performance
Product weight	0.077 Kg

Environment

Product certifications	CE[RETURN]CSA[RETURN]cURus[RETURN]EAC
Marking	CE
IP degree of protection	IP20
Ambient air temperature for operation	-10...55 °C
Ambient air temperature for storage	-20...85 °C
Relative humidity	10...90 % without condensation

Ordering and shipping details

Category	US1PC1222537
Discount Schedule	PC12
GTIN	3606480752513
Returnability	No
Country of origin	IT

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	13.200 Cm
Package 1 Width	9.100 Cm
Package 1 Length	18.700 Cm
Package 1 Weight	173.900 G
Unit Type of Package 2	S02
Number of Units in Package 2	6
Package 2 Height	15.000 Cm
Package 2 Width	30.000 Cm
Package 2 Length	40.000 Cm
Package 2 Weight	1.351 Kg

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is k
Mercury free	Yes
Sustainable packaging	Yes
Packaging made with recycled cardboard	Yes
REACH Regulation	Reference contains Substances of Very High Concern above the threshold 
EU RoHS Directive	Compliant By Exemption 
Take-back	No
WEEE Label	The product must be disposed on European Union markets following specific waste collection and neve

Contractual warranty

Warranty (in months)	18
----------------------	----

Product Life Status : **Commercialised**