

040812080

Aluminium Enclosure Aluform
80 x 120 x 81 mm

Aluminium Enclosure Aluform 80 x 120 x 81 mm

Catalogues | Assembly instructions | Declaration of Conformity | Drawing | 3D Data | Assignmentplan | Terminal Mounting

Technical data

Height	80 mm
Width	120 mm
Depth	81 mm
Material	Aluminium
Material quality	DIN EN 1706 EN AC-AlSi 12 (Fe)
Colour	Agate grey (RAL 7038)
Ingress protection	IP66
Degree of protection norm	EN 60529
Impact strength	IK09
temperature min.	-30 °C
temperature max.	80 °C
Seal material	PU (polyurethane) (standard)
Flame spread, sideways	HL 3
Rate of head dispersion	HL 3
Other versions on request	EMV, SBG, SWB, SBGL
Special colours on request	Yes
Approvals	LR (Lloyd's Register), UL (508A)

Commercial data

Country of origin	IN
Order unit	1 Piece
Customs tarif number	85369095
Weight	0.65 kg
GTIN	4250157901088

ETIM classification

ETIM 8	EC000058

ROSE SYSTEMTECHNIK GMBH
Erbeweg 13-15
32457 Porta Westfalica, Germany

Tel.: +49 571 50 41-0
Fax: +49 571 50 41-6
Mail: rose@rose-pw.de

Accessories

040000100
Aluform External hinges

040000200
Aluform Lid safety strip



040000800
Aluform External mounting bracket 80

100110610
Mounting plate for 04.081208