

FEATURES

- **Heavy Duty Design:**
Provides robust support for large cable bundles up to 372 mm in diameter
- **Nylon Material:** Offers durability and resistance to wear and tear
- **UV Resistant:** Suitable for outdoor use, resisting degradation from sunlight
- **High Tensile Strength:**
Supports up to 80 kg, ensuring secure fastening
- **Wide Operating Temperature Range:**
Functions effectively up to 85 °C, suitable for various environments
- **Fire Behaviour UL 94 V-2:**
Meets safety standards for flammability

RS PRO Heavy Duty Cable Tie, 1219 mm Nylon

RS Stock No: 656-068



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

RS PRO heavy duty cable ties are designed for secure and reliable bundling of cables and wires. With a length of 1219 mm, these cable ties are ideal for managing large bundles, ensuring a tidy and organised setup. Made from durable nylon, they offer excellent tensile strength and UV resistance, making them suitable for both indoor and outdoor applications.

General Specifications

Colour	Black
Product Type	Cable Tie
Sub Type	Heavy Duty Cable Tie
Tensile Strength	80 kg

Protection Category

Fire Behaviour	UL 94 V-2
UV Resistant	Yes

Mechanical Specifications

Length	1219 mm
Material	Nylon
Maximum Bundle Diameter	372 mm
Width	9 mm

Operation Environment Specifications

Maximum Operating Temperature	85 °C
-------------------------------	-------

Approvals

Standards/Approvals	ABS 15-TA1338482-PDA, CE 40022513, cULus E97527, DNV TAE00000US, LR 16-80006, RoHS, UL94V-2, VDE 40022513
---------------------	---