



Main

Range	Acti 9
Product name	Acti 9 iSW
Product or component type	Switch disconnecter
Device short name	ISW
Device application	Control Isolation
Poles description	1P
Utilisation category	AC-22A
Suitability for isolation	Yes

Complementary

[Ie] rated operational current	40 A 240 V AC 50/60 Hz
[Ue] rated operational voltage	240 V AC 50/60 Hz
[Icm] rated short-circuit making capacity	4.2 kA switch-disconnector alone
[Icw] rated short-time withstand current	1260 A
[Ui] rated insulation voltage	250 V AC 50/60 Hz
[Uimp] rated impulse withstand voltage	6 kV
Control type	Toggle
Local signalling	ON/OFF indication
Contact position indicator	Yes
Mounting mode	Fixed
Mounting support	DIN rail
Comb busbar and distribution block compatibility	Top or bottom : YES
9 mm pitches	2
Height	85 mm
Width	18 mm
Depth	73 mm

Colour	White
Mechanical durability	20000 cycles
Electrical durability	15000 cycles
Connections - terminals	Tunnel type terminals: (top or bottom) rigid Tunnel type terminals: (top or bottom) flexible Tunnel type terminals: (top or bottom) flexible with ferrule
Wire stripping length	9 mm
Tightening torque	3.5 N.m

Environment

Standards	EN 60947-3 IEC 60947-3
IP degree of protection	IP20
Pollution degree	3
Tropicalisation	2
Relative humidity	95 % at 55 °C
Ambient air temperature for operation	-25...60 °C
Ambient air temperature for storage	-40...85 °C

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0844 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------