

Rolling TV Cart/Stand On Wheels For 60-100inch Flat Screens Up To 220lb (100kg), Height Adjustment via Hand Crank, Mobile/Portable Trolley Mount

Product ID: 1110C-MOBILE-TV-CART



This height-adjustable rolling TV stand creates a mobile media center that can support 60 to 100-inch TVs and 220lb (100kg). Large casters enable users to move the mounted AV equipment with ease across an office, classroom, or trade show hall.

The crank handle allows the user to adjust the height of the TV without tools, from 47.2 to 65 inches (1200-1650mm) helping to accommodate different viewing needs. Height adjustment is possible even when a TV is already mounted, and the height indicators at the back of the column enable precise adjustments. The crank handle can be removed or locked to prevent tampering.

The +5/-10 screen tilt aids with viewing angles or reduces glare from overhead lights or windows for optimal viewing comfort.

For increased portability and customization, this mobile trolley features two independently height-adjustable media shelves under the display that can support up to 11lb (5kg) each. The webcam shelf sitting at the top of the display can be raised up to 93.1" (2366mm) from the floor.

The heavy-duty TV stand's aluminum and steel construction makes it ideal for commercial use in environments with multiple users and frequent movement between areas. Handles at the back of the columns combined with the 4-inch casters enable smooth transportation across different locations. Once in place, all wheels can be locked. Base dimensions 44.8x27.5in (1138mmx700mm).

Certifications, Reports and Compatibility

Applications

Features

- **ROLLING TV CART:** Heavy-duty aluminum portable TV stand on wheels fits 60 to 100in displays and supports up to 220lbs (100kg); 4in lockable casters; Move with handles on the columns; Sturdy steel base (44.8x27.5in/1138mmx700mm) helps prevent tipping
- **ADJUSTABLE HEIGHT:** Movable TV mount enables height adjustment even when a TV is mounted; Use the crank to adjust the height within a range of 47.2 to 65in (1200-1650mm) from the floor to the center of the screen; Height indicators for precise adjustment
- **EQUIPMENT STORAGE:** Includes two shelves that are height-adjustable independently from the display; Each shelf supports 11lb (5kg); Webcam shelf can be raised up to 93.1" (2366mm), while the lower media shelf can rise up to 35.4" (900mm) from the floor
- **COMPATIBILITY:** Universal television cart supports flat TVs, curved TVs, and smart or interactive displays that feature compatible VESA patterns of 200x200, 300x200, 300x300, 400x200, 400x400, 600x400, 800x400 and 1000x600
- **MOBILE PRESENTATION CART:** Silver rolling TV trolley moves a large display with its equipment within offices, trade shows, and educational environments; Integrated cable management keeps cables organized for clutter-free installation and seamless mobility

Hardware

Warranty	5 Years
Cable Management	Yes
Tools Included	Yes
Casters	Included
# of Displays Supported	1
Orientation	Horizontal
Mounting Options	Mobile Cart
VESA Hole Pattern(s)	200x200 mm
	300x200 mm
	300x300 mm
	400x200 mm
	400x300 mm
	400x400 mm
	600x400 mm

800x400 mm

1000x600 mm

Performance

Weight Capacity of Work Surface	176.5 oz [5000 g]
Minimum Display Size	60"
Maximum Display Size	100"
Fits Curved Display	Yes
Video Wall	No
Height Adjustment	Yes
Minimum Height	47.2 in [1200 mm]
Maximum Height	65.0 in [1650 mm]
Display Tilt	+ 5 / - 10
Anti-theft	No

Physical Characteristics

Color	Black & Silver
Construction Material	Aluminum, Steel, and Plastic
Product Length	4.1 ft [1.2 m]
Product Width	29.7 in [75.5 cm]
Product Height	7.8 ft [2.4 m]
Weight of Product	84.1 lb [38.2 kg]

Packaging Information

Flat Pack (Assembly Required)	Yes
Package Length	22.6 in [57.5 cm]
Package Width	3.9 ft [1.2 m]

Package Height	9.5 in [24.2 cm]
Shipping (Package) Weight	90.0 lb [40.8 kg]

What's in the Box

Included in Package	1 - Base
	1 - Left Leg
	1 - Right Leg
	1 - Left Leg Cover
	1 - Right Leg Cover
	1 - Universal Plate
	2 - Universal Plate Endcaps
	2 - Grab Handles
	4 - Casters
	1 - Left Column
	1 - Right Column
	1 - Crank Handle
	1 - TV Bracket, Right
	1 - TV Bracket, Left
	2 - Column Top Cover
	1 - Camera Shelf
	1 - Shelf #1
	1 - Shelf #2
	1 - Camera Shelf Plate
	1 - Connecting Bar
	1 - M5 x 40mm Screw
	4 - M6 x 25 Screws

- 3 - M4 x 6mm Screws
- 2 - M4 x 6mm Screws
- 4 - M6 x 14mm Screws
- 12 - M8 x 25mm Screws
- 12 - M6 x 8mm Screws
- 4 - M5 x 14mm Screws
- 4 - M6 x 14mm Screws
- 4 - M6 x 30mm Screws
- 4 - M8 x 30mm Screws
- 4 - M8 x 50mm Screws
- 4 - Washers
- 8 - Small Spacers (15mm x 8mm x 5)
- 8 - Large Spacers (15mm x 8mm x 15)
- 1 - 5mm Hex Key
- 1 - 19mm Wrench
- 8 - Adhesive Cable Management Clips
- 1 - Manual

****Product appearance and specifications are subject to change without notice.***