

## Product information

# 18V 13MM 2 SPEED LXT DRILL DRIVER



### BDF456RFE

Battery Type	Lithium-ion
Max. in steel	13 mm
Max. in wood	38 mm
Vibration drilling	2.5 m/sec <sup>2</sup>
Battery quantity (3.0 Ah)	2
No load speed	H: 0 - 1500 / L: 0 - 400 rpm
Vibration K factor	1.5 m/sec <sup>2</sup>
Noise sound pressure	70 dB(A)
Noise K factor	3 dB(A)
Net weight	1.7 kg
Voltage	18 v
Max torque S/H	32/50 Nm
Torque settings	16



- 22 minute charge time with the air cooled Makstar Optimum Charging System.
- 4 pole motor.
- High comfort grips.
- Conveniently located push button for forward and reverse.
- LED job light with afterglow.
- Lithium-ion batteries have greater life spans than their Ni-MH or Ni-Cad counterparts giving 430% greater run time.
- Lithium-ion's 40% weight saving means 18 volt power can be obtained by a battery that weighs the same as a 12 volt Ni-MH battery.
- Metal gears
- Keyless chuck.
- Two speed gear box.

Details correct as of: 31-1-2012

Makita reserve the right to change specifications at any time owing to their policy of constant improvement.

Accessories shown are not necessarily supplied.

[www.makitauk.com](http://www.makitauk.com)