






REV.	ECN NO.	DATE	SIGN	DESCRIPTION
A		2025-03-03	Henry	Rev.01 To Rev.A
B	C250706	2025-05-28	Henry	 X2



Note:

- * **Ⓞ Important Dimension.**
- * Waterproof Rate: IP68(2m/1h)
- * Body: PC, Gray.
- * Membrane: ePTFE
- * O-Ring: Rubber, Black.
- * Air Permeability: >16L/min @1.2 kPa
- * Temperature Resistance: -40~125℃
- * Recommended installing torque: 5N.m
- * Recommended plate thickness: T > 4.0mm.
- * All Parts Are RoHS Compliant.

UNIT: mm				TITLE BREATHABLE VENT, PLASTIC, M32		Amphenol LTW 安費諾亮泰企業股份有限公司		ITEM NO VT-BPM32GY-NO8001		DRAWN BY Henry		DATE 2025-05-28			
TOLERANCE .X ±0.25 .XX ±0.1 .XXX ±0.05 ANGLES ±		SCALE 2:3		SIZE A4				SHEET 1 OF 1		DWG NO VT-BPM32GY-NO8001		CHECKED BY Jerry		DATE 2025-05-28	
		REV. B		WC-REV. .0				QC: Inspection item		CUSTOMER ALTW		APPROVED BY Fred		DATE 2025-05-28	