

## 222A.TJ - Sets of ground twist drills




### Standards:

**NF ISO 235, ISO 235, DIN 338**

### Description:

- For steel up to 800 MPA, stainless steel, grey cast-iron and aluminium alloy.
- Sets 222A.TJ19 and 222A.TJ25: Bits with 5/10 mm increments.
- Sets 222A.TJ50 and 222A.TJ81: Bits with 1/10 mm increments.

	Depth [mm]	Diameter D Maxi [mm]	Length L [mm]	Height H [mm]	Dimensions [mm]	Weight [g]	CONTENT SET []
<b>222A.TJ19</b>	165.0	1 - 10	110.0	35.0	165 x 110 x 35	730.0	19
<b>222A.TJ25</b>	190.0	1 - 13	110.0	54.0	190 x 110 x 54	1390.0	25
<b>222A.TJ50</b>		1 - 5.9	120.0	35.0	135 x 120 x 35	760.0	50
<b>222A.TJ81</b>	235.0	2 - 10	210.0	145.0	235 x 210 x 145	760.0	81